

Low Speed Saw

CL40

**Precision
cutting
low noise and
low vibration**


**Various vises
for different
requirement**



Instruction



Operation video



Cover

Easy for observation

Micrometer

Easy to control cutting length

Vise

Various vises to meet the request

Cutting

Gravity feed system

Cut off blade

To choose the blade per sample material

Control panel





Friendly interface
Intuitive buttons

Coolant tray

Removable coolant reservoir, easy to pick up the sample after cutting



Features

CL400051A irregular vise kit	CL400052-L (option) Long type kit (φ20)	CL400044A (standard) Long type kit
		
CL400053 Round/elliptic vise kit	Options Standard 	
CL400054 Fragile vise		
		
CL400055-D Double vise kit		
		
CL50051001A Round test kit (max.Ø32)		

Micrometer

Minimum display precision 0.01mm
Clamp horizontal movement distance: 25mm



Options

Standard

Coolant tray

Easy to change coolant and easy to pick up sample after cutting



Control panel

Easy to operate
Adjust the cutting speed depending on sample material

Please refer to Appendix 1 and Appendix 2 for the cutting capacity

Worthy Options - Working Table




Working Table

Multifunctional working table, it supplies you a place to put your machine and store your accessories. It can be moved easily.

Model No.	TF01	TF02
Size	1000*800*700 mm	1000*1200*700 mm
Sample		

Appendix 1: Cutting capacity for vise (standard)






Cut-off blade	●		■	
	A(mm)	A cutting area(mm ²)	E(mm)	E x D(mm ²)
3"	15	170	15	15x5
4"	28	610	40	40x12
5"	40	1250	40	40x25




The measure of square area :

Max width is E , $E \times D \leq A$ cutting area

Material restrictions are non-ferrous metals, non-metallic, ceramic, glass, titanium, precision cutting, polymer materials

Appendix 2: Cutting capacity for various vises (options)

CL400051A irregular vise kit		CL400052-L Long type kit (φ20)		CL400053 Round/elliptic vise kit	
					
A (mm)	E x D (mm)	A (mm)	E x D (mm)	A (mm)	E x D (mm)
–	38x25	Max. 20	40x30	Max. 14	38x10
					



CL400054 Fragile vise		CL400055-D Double vise kit		CL50051001A Round test kit	
					
A (mm)	E x D (mm)	A (mm)	E x D (mm)	A (mm)	E x D (mm)
Max. 28	50x28	Max. 20	40x30	Max. 32	–
					



TOP TECH



Specification

Model	CL40
Motor power	40W
Sample Dim. Max.(mm)	Ø40mm
Diamond blade	Ø3"~ Ø5"
Noise level	55~62dB
Cutting chamber	Appendix 3
Loading pressure	0~400g
Cutting Method	Gravity-fed system, the blade stop rotating once cutting finished
Rotational speed	0~400 RPM
Vise (standard)	Long type kit
Horizontal movement	0.01 mm ~ 25 mm
Coolant tank capacity	400 mL
Machine size (W x L x H)	44 x 42 x 35cm
Machine weight Kg	19 Kg
Power	AC110V/200V-1Ø
Standard accessory	coolant 1 L 、standard clamp*1
Options	Various vise, dressing system



Parameter

Cutting Capacity-1 CL40



Cutting area-1 : Use standard clamp

1. Parameter for reference only.
2. Practically parameter depends on wheel, sample material, cutting speed, vise, etc.

Consumables

Diamond Wheel

Item No.	Cutting material	Wheel size(external dia. X arbor dia. X thickness)	MOQ	Remark
HW21130502L	Hard, brittle, mineral material, non-ferrous metals ,hard alloy, ceramic, glass, titanium alloy, quartz, silicon	Ø101XØ12.7X0.5	1	resin-bonded
HW21120502L	Non-ferrous metals , non-mental, ceramic, glass, titanium alloy, aluminum alloy, tungsten steel	Ø100XØ12.7X0.5	1	metal-bonded
HW21220502L	Carbon steel, alloy steel, tool steel, stainless steel, bearing steel	Ø100XØ12.7X0.5	1	CBN metal-bonded (boron nitride)
HW21130602L	Hard, brittle, mineral material, non-ferrous metals ,hard alloy, ceramic, glass, titanium alloy, quartz, silicon	Ø127XØ12.7X0.6	1	resin-bonded
HW21120602L	Non-ferrous metals , non-mental, ceramic, glass, titanium alloy, aluminum alloy, tungsten steel	Ø125XØ12.7X0.5	1	metal-bonded
HW21220602L	Carbon steel, alloy steel, tool steel, stainless steel, bearing steel	Ø127XØ12.7X0.5	1	CBN metal-bonded (boron nitride)

Coolant


Item No.	Description	Features	MOQ	Remark
S01004	Coolant	Clear , flowability	1L	

Remark: Please access following link for details of consumables

<http://toptech.synology.me/Consumables/CuttingEN.pdf>



Appendix 3 : Cutting chamber





*Perfect Surface.
Always*

Cutting / Mounting / Grinding & Polishing / Spin Coater

TOP TECH MACHINES CO.,LTD

No.6-3, Siayuan Rd., Dali, Taichung, 412 Taiwan

Tel: 886-4-24061658

Fax: 886-4-24073200

<http://www.toptech.tw>

<http://toptech.sniapp.com>

E-mail: top@toptech.tw

Agent



All right reserved by Top Tech

NO.A16-01

<http://www.toptech.tw>